

VALUELINE

DVI Cable DVI-D 24+1-Pin Male - DVI-D 24+1-Pin Male 3.00 m Black

General information

With this DVI-D cable you can transmit digital signals between for example a computer and a LCD monitor.

Specifications

Connector design - side B:	Straight
Diameter:	7.5 mm
AWG value:	30
Plating:	Nickel
Max. resolution:	2560x1600
Length:	3.00 m
Cable design:	Round
Connector design - side A:	Straight
Outside material:	PVC
Packaging:	Polybag
Conductor material:	Copper
Colour:	Black
Connection B:	DVI-D 24+1-Pin Male
Cable type:	DVI
Connection A:	DVI-D 24+1-Pin Male

Package contents

- 1x DVI cable



Sales information

Order code:	VLCP32000B30
Product description:	DVI Cable DVI-D 24+1-Pin Male - DVI-D 24+1-Pin Male 3.00 m Black
Packaging:	Polybag
Brand name:	Valueline



Quantity	LxWxH (mm)	Weight
1	155x40x200	279 gr.
30	315x310x405	8900 gr.
40	335x290x395	10600 gr.