

# VALUELINE

## Notebook Adapter 15 / 19.5 VDC 70 W

### General information

Universal notebook adapter to charge nearly any type of notebook. The adapter is supplied with 10 different and easily changeable power tips, which are compatible with the following brands: TOSHIBA, LENOVO, IBM, SONY VAIO TZ series, SAMSUNG, FUJITSU, DELL, COMPAQ, ACER, HP, LG, BEN Q, CHROMEBOOK 14 and NEC. If the required tip is not included, please send an e-mail to [service@nedis.com](mailto:service@nedis.com) and it will be provided for free.

In addition, the notebook adapter is equipped with an easily replaceable, detachable AC cable, which reduces the risk of breaking or damage caused by frequent use.

### Features

- Over current, voltage, temperature and overload protection
- Detachable AC cable, which reduces the risk of breaking caused by frequent use
- 10 different, easily changeable power tips to charge nearly any type of notebook

### Specifications

Height:	31 mm
Width:	47.5 mm
Output voltage selection:	Manually
Charger type:	Home
Charger type:	Notebook
Output plug type:	5.5 x 2.5 mm
Output plug type:	6.3 x 3.0 mm
Output plug type:	6.5 x 1.4 mm
Output plug type:	5.0 x 3.4 mm
Output plug type:	7.4 x 5.1 mm
Output plug type:	7.9 x 5.6 mm
Output plug type:	4.75 x 1.7 mm



### Sales information

Order code:	<b>CSUNA70RBL</b>
Product description:	Notebook Adapter 15 / 19.5 VDC 70 W
Packaging:	Giftbox with eurolock
Brand name:	Valueline



Quantity	LxWxH (mm)	Weight
1	155x65x255	531 gr.
10	335x180x555	5860 gr.
20	350x395x570	12260 gr.

# VALUELINE

## Notebook Adapter 15 / 19.5 VDC 70 W

Output plug type:	5.5 x 1.75 mm
Output plug type:	4.5 x 3.0 mm
Output plug type:	11.0 x 4.6 mm
Cable length:	3.30 m
Output power:	70 W
Voltage:	AC 100 - 240 V
Power plug:	Euro / Type C (CEE 7/16)
Output voltage:	15 VDC
Output voltage:	19.5 VDC
Length:	113.15 mm

### Package contents

- 1x adapter
- 10x power tips
- Manual