

VALUELINE

CAT7 PiMF (S/FTP) Network Cable RJ45 (8P8C) Male - RJ45 (8P8C) Male 1.00 m Grey

General information

Double-shielded patch cable for CAT7 installations, suitable for 10/100/1000/10000 megabit network environments.

Features

- CAT7 technology supporting 10, 100, 1000 and 10000 Mbps ethernet
- Full copper conductor to ensure superior transmission properties
- Flexible strain relief to avoid cable fractures
- Durable moulded connectors specifically designed for intensive usage
- Low Smoke Zero Halogen (LSZH) jacket.

Specifications

AWG value:	26
Diameter:	5.8 mm
Plating:	Gold
Length:	1.00 m
Colour:	Grey
Cable design:	Round
Version:	1:1
Shielding:	PiMF
Outside material:	PVC LSZH
Packaging:	Polybag
Conductor material:	Copper
Connection B:	RJ45 (8P8C) Male
Connection A:	RJ45 (8P8C) Male
Cable type:	CAT7



Sales information

Order code:	VLCP85420E10
Product description:	CAT7 PiMF (S/FTP) Network Cable RJ45 (8P8C) Male - RJ45 (8P8C) Male 1.00 m Grey
Packaging:	Polybag
Brand name:	Valueline



Quantity	LxWxH (mm)	Weight
1	180x25x145	49 gr.
180	355x350x440	8840 gr.