

## NiMH Battery Charger AA/AAA 4x AA/HR6 2600 mAh

## General information

Fast, compact charger for home use or on the road. The charger is able to charge 4 batteries at the same time. Includes 4x AA batteries, a 12 V adapter and a cable to charge the batteries via USB. Suitable for use all over the world (110V - 240 V 50/60Hz).

- Blue LCD information display
- Suitable to charge 2700 mAh & 1000 mAh
- Switch off: timer, Minus Delta V
- Overheating protection
- Trickel charing
- Quick charging (2-4 hours)
- Detects battery damage
- Wrong polarity protection
- 4 Indication LEDs

## Specifications

Indication of charging status:	LCD
Trickle Charging:	Yes
Charger type:	Home Desktop
Charger type:	Car
Input voltage:	12 VDC
Input voltage:	100-240 VAC
Batteries included:	4x AA/HR6 2600 mAh
Safety functions:	Overheat Protection
Safety functions:	Safety Timer
Safety functions:	Minus Delta V
Cable length:	1 m
No. of batteries supported:	2
No. of batteries supported:	4
Power plug:	Euro / Type C (CEE 7/16)
Power plug:	Car Adapter
Power plug:	USB
Battery type:	AA
Battery type:	AAA
Technology:	NiMH



Sales information		
Order code: Product description:	<b>VARTA-POWERLCD</b> NiMH Battery Charger AA/AAA 4x AA/HR6 2600 mAh	
Brand name:	Varta	

Quantity	LxWxH (mm)	Weight
1	125x90x232 130x135x280	424 gr. 934 gr.
2	130x135x280	934 gr.



## NiMH Battery Charger AA/AAA 4x AA/HR6 2600 mAh

Output voltage:

1.2 VDC

Information is subject to change without prior notice. Contents may differ from what is shown. Supplier can not be held responsible, nor liable for the information contained in this document. This document was generated at 03/09/2018 11:03:28