

MINI REED SWITCH

 velleman.eu/products/view



Features

- housing: grey ABS
- miniature magnetic switch NC (when activated by magnet)
- screw mounting

Specifications

- contact: NC
- switching voltage (max): 1-50 V AC/DC
- switching current (max.): 100 mA
- contact capacity (max.): 5 W
- initial contact: 0.2 ohm max.
- carry current (max.): 100 mA
- breakdown voltage: 150 VDC
- insulation resistance: 100M ohm min.
- switch cycle: 5 x 10⁷ @ 12 VDC, 50 mA
- with leads (on switch): 300 mm
- operating gap: max. 23 mm
- dimensions: 34 x 15 x 8 mm