

MAGNETIC SWITCH - 0.1 A @ 30 VDC - NC - LEAD WIRES

 velleman.eu/products/view

HAA306



Features

- recessed mount
- Oki reed switch
- can be used for metal doors (depending on the installation, application, and size of the metal door)

Specifications

- colour: white
- contact: closed loop, normal closed
- gap width: 15mm
- wire length: ± 25 cm
- mount: recessed mount $\text{\O}9$ mm (1/3"), press fit
- contact rating: 0.1 A @ 30 VDC
- dimensions: $\text{\O}9$ x 14.5mm
- weight: 7g