

COUNTDOWN/-UP TIMER WITH ALARM

 velleman.eu/products/view

TIMER10N



Features

- count down or up: max. 99 min. 59 sec.
- mounting: clip or magnet
- can also be placed upright

Specifications

Physical Properties

Display

Display Height 17 cm

Display Width 38 cm

Display Type LCD

Set-up Options

Maximum Timer Setting 99 m

Timer Type Digital

Power Supply

Battery
Required

Power Supply

Number of Batteries 1

Batteries

Battery IEC Size SR44 (LR1154, SR1154, 1166A, 1107SO, 1131SOP, AG13, SG13, LR44, LR154, A76, S76, EPX76, 157, 303, 357, 1128MP, AG-14, CA18, CA19, CR44, D76A, G13A, G13-A, GDA76, GP76A, GPA7, GPA75, GPA76, GPS76A, KA, KA76, AG76, L1154, L1154C, L1154F, L1154G, L1154H, LR44G, LR44GD, LR44H, MS76H, PX76A, PX675A, RPX675, RW82, SB-F9, V13G, 357A)

Battery Composition Silver-Oxide

Battery Voltage Rating 1.5 V

Product Basic Info

Colour White

Height 44 mm

Depth 21 mm

Width 76 mm

Weight ± 35 g

Material ABS