

V3 MAX USB Drive 32GB | USB V3 MAX

www.verbatim-europe.co.uk/en/prod/v3-max-usb-drive-32gb-49806

Overview

Featuring a USB 3.2 Gen 1 interface for SuperSpeed data transfer, the Store 'n' Go V3 MAX USB Drive offers data transfer speeds of up to 300MB/sec. making it faster for transferring and saving larger file sizes of all types.

The design of the V3 MAX USB Drive also ensures that the USB connectors are protected featuring a 'slide and lock' mechanism. This locks into position when using the drive and retracts back into a closed position to protect the connector when not in use. The smooth, highly polished UV coating provides the USB drive with scratch protection, keeping it in pristine condition despite its usage!

Simple and easy to use, just plug into any USB 3.2 Gen 1 port (also compatible with USB 2.0) and drag and drop your folders and files.

Product Details

Part Number: 49806

Capacity: 32GB

- SuperSpeed USB 5Gbps.
- Up to 300MB/sec transfer speed.
- 'Slide and Lock' mechanism protects the USB connector when not in use.
- Smooth, highly polished finish.

System Requirements

USB 3.2 Gen 1 (USB 3.0) / USB 2.0 ports

Windows 10, 8, 7, Vista, XP

Mac OS X 10.4 or higher

Linux 2.4.0 or higher

Specifications

- Product Weight: 10 grams
- Product Dimensions: 58mm x 20mm x 11mm (L x W x H)
- Data Retention: 10 Years
- Power Source: USB Bus (no batteries required)
- Interface: USB 3.2 Gen 1 - backwards compatible with USB 2.0
- Format: FAT32

Pack Contents

Store 'n' Go V3 MAX USB Drive