

Store 'n' Go Secure Portable HDD with Keypad Access 2TB

[verbatim-europe.co.uk/en/prod/store-n-go-secure-portable-hdd-with-keypad-access-2tb-53403](https://www.verbatim-europe.co.uk/en/prod/store-n-go-secure-portable-hdd-with-keypad-access-2tb-53403)

In today's world, the security of your confidential data is of the utmost importance. Imagine losing your personal files, leaving them on a train or in the back of a taxi, knowing that anyone can access them because they were saved on a standard hard drive. Now the Store 'n' Go Secure with Keypad Access is here for your peace of mind.

The AES 256-bit Hardware Encryption seamlessly encrypts all data on the drive in real-time with a built-in keypad for password input. The hard drive does not store passwords in the computer or system's volatile memory making it far more secure than software encryption. Also, if it falls into the wrong hands, the hard drive will lock and require re-formatting after 20 failed password attempts.

Compatible with both PC and Mac operating systems, the hard drive interface is USB 3.1 GEN 1 with USB-C connection for super-fast data transfer speeds*. The pack includes a USB-C to USB-A cable as well as a USB-A to USB-C adapter for connection to a range of devices. It can also be connected to TVs, a feature which is not possible with regular encrypted hard drives.

For added security, Nero Backup software is provided to help you back up all your files, folders, and drives from your laptop or PC whenever you want. It also allows you to schedule an auto back up to a set time and day to ensure that it gets done regularly! Nero Backup Software is compatible with Windows Vista, Windows 7, Windows 8 and Windows 10 (not compatible with Mac OS).

Product Details

Part Number: 53403

- AES 256-bit Hardware Encryption, seamlessly encrypts all data on the drive in real-time
- Built-in keypad for password input
- Can be used with TVs (feature not possible with regular encrypted HDDs)
- USB 3.1 GEN 1 with USB-C™ connection
- Includes USB-C™ to USB-A cable (plus USB-A to USB-C™ adapter)
- LED power / encryption status indicators
- Does not store password in the computer or the system's volatile memory, therefore far more secure than software encryption

- PC and Mac compatible
- Combined aluminium / plastic enclosure

System Requirements

USB 3.1 GEN 1 (also compatible with USB 3.0/2.0)*

PC:

- Minimum Intel Processor Pentium II/50MHZ, 64MB RAM
- Windows 10, 8, 7

MAC:

- Minimum Apple G Processor, 64MB RAM
- Mac OS X 10.4 or higher

*for optimal performance, the drive must be connected to a USB 3.1 GEN 1 host controller

Specifications

- Power: Bus powered via USB cable
- Interface: USB 3.1 GEN 1
- Enclosure material: Plastic and Aluminium
- LED Indicator: Power, HDD / SSD activity and encrypted status
- Product Weight: 283 grams (approx)
- Dimensions: 123.5mm x 76mm x 11mm (L x W x H)
- Operating Temperature: 5°C to 50°C
- Storage Temperature: -40°C to 70°C
- Operating Humidity: 5 to 90%, non condensing

Pack Contents

Store 'n' Go Secure Portable HDD with Keypad Access
USB-C™ to USB-A Cable (includes USB-A to USB-C™ adapter)
Nero Backup Software (not compatible with Mac OS)
Quick Start Guide