

HDD Purple 8TB 3.5 SATA 6Gbs 128MB(WD80PURZ)
HDD Purple 8TB 3.5 SATA 6Gbs 128MB



WD Purple drives are built for 24/7,always-on,high-definition security systems. With a high workload rate,WD Purple drives are optimized for surveillance systems. WD Purple surveillance storage also features WD's exclusive AllFrame 4K technology,so you can confidently create a security system tailored to the needs of your business.

Key Selling Points

Surveillance you can trust
WD's exclusive AllFrame 4K technology
Enhanced workload rating
Wide compatibility,seamless integration
Less power,more efficient

Product Features

Surveillance you can trust

With WD Purple surveillance storage,you have a drive engineered for high temperature,always-on surveillance systems so you can rely on quality video playback when you need it most. Whether you're protecting loved ones or monitoring your business,WD Purple offers performance you can trust.

WD's exclusive AllFrame 4K technology

All WD Purple drives are equipped with AllFrame 4K technology,which improves ATA streaming to help reduce frame loss,improve overall video playback,and increase the number of hard drive bays supported within a NVR. Futureproof your surveillance solution knowing that WD Purple is ready for ultra high definition cameras.

Enhanced workload rating

With a high workload rating WD Purple is designed to handle the unique demands of modern video surveillance DVR and NVR systems.

Wide compatibility,seamless integration

WD Purple hard drives are built with compatibility in mind,so you can quickly and seamlessly add capacity to your surveillance system. With a wide range of enclosures and chipsets supported,you're sure to find the DVR or NVR configuration that's right for you.

Less power,more efficient

With exclusive IntelliSeek technology,WD Purple drives are able to calculate optimum seek speeds. This keeps power consumption low so ambient noise and vibrations are at a minimum.

Main Specifications

Product Description	WD Purple Surveillance Hard Drive WD80PURZ - hard drive - 8 TB - SATA 6Gb/s
Type	Hard drive - internal
Capacity	8 TB
Form Factor	3.5"
Interface	SATA 6Gb/s
Data Transfer Rate	600 MBps
Buffer Size	128 MB
Spindle Speed	5400 rpm
Features	Time-Limited Error Recovery (TLER),Advanced Format technology,HelioSeal,surveillance system compatible,24x7 availability,Write-Intensive Endurance,AllFrame 4K
Dimensions (WxDxH)	101.6 mm x 147 mm x 26.1 mm
Weight	650 g
Localisation	Worldwide
Manufacturer Warranty	3 years warranty

Extended Specification

General

Device Type	Hard drive - internal
Capacity	8 TB
Form Factor	3.5"
Interface	SATA 6Gb/s
Buffer Size	128 MB
Features	Time-Limited Error Recovery (TLER),Advanced Format technology,HelioSeal,surveillance system compatible,24x7 availability,Write-Intensive Endurance,AllFrame 4K
Width	101.6 mm
Depth	147 mm
Height	26.1 mm
Weight	650 g

Performance

Drive Transfer Rate	600 MBps (external)
Internal Data Rate	178 MBps
Spindle Speed	5400 rpm

Reliability

Non-Recoverable Errors	1 per 10 ¹⁴
Load / Unload Cycles	300,000

Expansion &Connectivity

Interfaces	1 x SATA 6 Gb/s
Compatible Bay	3.5"

Power

Power Consumption	6.4 Watt (read) 6.4 Watt (write) 5.7 Watt (idle) 0.7 Watt (standby) 0.7 Watt (sleep)
-------------------	--

Miscellaneous

Compliant Standards	Directive 2002/95/EC
Localisation	Worldwide

Manufacturer Warranty

Service &Support	Limited warranty - 3 years
------------------	----------------------------

Environmental Parameters

Min Operating Temperature	0 °C
Max Operating Temperature	65 °C
Min Storage Temperature	-40 °C
Max Storage Temperature	70 °C

Shock Tolerance (operating)	30 g @ 2 ms
-----------------------------	-------------

Shock Tolerance (non-operating)	250 g @ 2 ms
------------------------------------	--------------

Sound Emission	29 dBA
----------------	--------

Computer 2000 is not responsible for the errors in the documentation of products