



MY BOOK™ DUO

DESKTOP RAID STORAGE

Massive Storage. Impressive Drive.

- Massive capacity storage with auto and system backups
- RAID-0 ready out of the box
- RAID-optimized WD™ drives
- USB 3.1 Gen 1 ready, USB 3.0 compatibility

The My Book™ Duo drive has massive capacity ideal for storing photos, videos, documents and music. It's super-fast with up to 360MB/s¹ sequential read speeds of the USB Type-C™ port. That USB Type-C port with all cables included makes it universally compatible (supports USB 3.1 Gen 1/3.0/2.0). Two USB Type-A hub ports deliver flexibility for additional accessories.





MY BOOK™ DUO DESKTOP RAID STORAGE



Product Features

Massive Capacity

The My Book™ Duo drive has up to 36TB² capacity with a single cable. Free up valuable space on all your computers. Store and back up your photo, video and music collections, and important documents in one reliable place.

RAID-0 Ready Out of the Box

Ready to perform at maximum speed and capacity in default mode, RAID-0. Reconfigure the drive to RAID-1 for redundancy (data mirroring), or use it as two independent drives (JBOD) with the included WD Drive Utilities™ software.

RAID-Optimized Drives

The My Book™ Duo drive comes with RAID-optimized WD™ drives inside to deliver high-speed, quality storage to rely on. RAID-optimized firmware is perfect for two-disk array systems with auto management of drive operations to help ensure read/write cycle data integrity.

USB 3.1 Gen 1 Ready, USB 3.0 Compatibility

Compatible with USB 3.1 Gen 1 and USB 3.0, the My Book™ Duo drive works to deliver high-speed connectivity no matter the interface. Includes both USB Type-C™ to Type-C and Type-C to Type-A cables.

Product Specifications

CAPACITIES AND MODELS

36TB WDBFBE0360JBK
28TB WDBFBE0280JBK
24TB WDBFBE0240JBK
20TB WDBFBE0200JBK
16TB WDBFBE0160JBK
12TB WDBFBE0120JBK

CONTENTS

- Desktop RAID storage
- WD Discovery™ software for WD Backup™, WD Security™ and WD Drive Utilities™
- USB-C to USB-C cable
- USB-C to USB-A cable
- AC adapter
- Disk replacement tool
- Quick install guide

INTERFACE

USB 3.1 Gen 1 Type-C up to 5Gb/s
USB 3.0 Type-A up to 5Gb/s
Power Supply (DC in)

DIMENSIONS

Length: 160 mm (6.30 in)
Width: 100 mm (3.94)
Height: 180 mm (7.09)

Weight: 36TB - 2.46 kg (5.42 lbs)
28TB - 2.46 kg (5.42 lbs)
24TB - 2.40 kg (5.29 lbs)
20TB - 2.38 kg (5.25 lbs)
16TB - 2.36 kg (5.20 lbs)
12TB - 2.52 kg (5.56 lbs)

OPERATING SPECIFICATIONS

Operating temperature:
5°C to 35°C
Non-operating temperature:
-20°C to 65°C

SYSTEM COMPATIBILITY

- Windows® 10 or Windows 8.1 operating systems
- macOS® (reformatting required)

Compatibility may vary depending on user's hardware configuration and operating system.

LIMITED WARRANTY

3 years



¹As used for sequential read transfer rate, megabyte per second (MB/s) - one million bytes per second.

²As used for storage capacity, one terabyte (TB) = one trillion bytes. Total accessible capacity varies depending on operating environment and RAID/JBOD configuration.

WD, the WD logo, My Book, WD Backup, WD Discovery, WD Drive Utilities, WD Red and WD Security are registered trademarks or trademarks of Western Digital Corporation or its affiliates in the US and/or other countries. Mac, the Mac logo and macOS are trademarks of Apple, Inc. USB Type-C is a trademark of USB Implementers Forum, Inc. All other marks are the property of their respective owners. Product specifications subject to change without notice. Pictures shown may vary from actual products.

©2021 Western Digital Corporation or its affiliates. All rights reserved.