

WHA 3000PS

Product no.: T0053355699N



Benefits

- > 700 W
- > Integrated turbine
- > Set with Infrared preheating plate and circuit board holder



For this purpose, we recommend:



Solder fume extractors



Pre-heating plates



Zubehoer



Soldering tips



Technical Data

Dimensions L x W x H (inches)	9,44 x 10,63 x 6,69
Dimensions L x W x H (mm)	240 x 270 x 170 (WHA3000P)
Space requirement/workspace L x W x H (inches)	23,6 x 23,6 x 19,7 (WHA3000P + WBHS + WHP3000)
Space requirement/workspace L x W x H (mm)	600 x 600 x 500 (WHA3000P + WBHS + WHP3000)
Recommended assembly size (mm)	310 x 320
Recommended component size (mm)	4,5 x 4,5 - 43x43
Compressed air connection	X
Compressed air connection accessory	X
Compressed air supply kPa/bar	X
Air consumption l/min	X
Max. hot air flow rate l/min	5 - 50
ESD-safe	on
Noise level (distance 1 m) dB(A)	tbd
Weight (approx.) in kg	tbd
Power consumption	1200 W
Rated output of top heating (W)	700
Rated output of bottom heating (W)	600
Protection class	1 (control unit and hand piece hard grounded)
Voltage	220-230V/50-60Hz
Temperature range of top heating (°C)	50 - 500
Temperature range of bottom heating (°C)	50 - 400
Optical positioning	---
Positioning aid	X
Temperature accuracy of top heating	± 30 °C (± 54 °F)
Temperature accuracy of bottom heating	tbd
Thermocouple connection	1x Type-K

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE