

**WI-M-20-XX-@**  
(20 AWG, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-20-@ is 20 AWG, 41/0.127 stranded, tinned copper wire with highly flexible 0.088" (2.24mm) diameter silicone jacket.
- Ratings:

Current	14 Amps @ 150°C
Voltage	600V
Dielectric Strength	2 KV/Min
Spark Test	8 KV
Bend Radius	3D
Rated Temperature	-40°C to 200°C
Temperature Rating	FT2
- Length: The "XX" in the model number indicated length in feet.  
Standard lengths: 10', 25', 30', 50', and 100'
- Color: The "@" in the model number represents color.  
Available colors: -0 Black, -2 Red