

Wi-Fi Smart LED Filament Bulb | E27 | A60 | 5 W | 500 lm | Clear

General information

This smart filament bulb combines modern day technology with classic looks. It connects directly to your wireless/Wi-Fi router to offer remote and automatic control.

Easy to set up

You don't need to be a technical genius or an electrician to control and automate your lighting remotely. All you actually need is your Wi-Fi router, our intuitive app and this Nedis® Wireless Smart Bulb. No extra kit and no connecting hubs: this is home automation made simple.

Control the bulb's brightness

Connect it up and you can now control the brightness by using your smartphone or tablet. And if you're getting super smart you can even control it with your voice via Amazon Alexa or Google Home.

Set up schedules and pair with other smart products

Set up time schedules for the bulb to be switched on or create ambient scenes in an instant by pairing this bulb to other products from the Nedis® SmartLife range.

About Nedis® SmartLife

Discover a wide and ever-expanding range of products - such as bulbs, switches, sockets, sensors, and cameras - that can all be controlled through an easy-to-use and intuitive app. With voice control features supported by Amazon Alexa and Google Home, and no need for anything more than your existing Wi-Fi network, this is the connected, smart home made simple. Whether you're looking for a single smart bulb or socket, or you want to automate your entire house, discover how accessible smart technology is today.

Features

- Connects directly to your wireless/Wi-Fi router - to offer



Sales information

Order code: **WIFIL10WTA60**
 Product description: Wi-Fi Smart LED Filament Bulb | E27 | A60 | 5 W | 500 lm | Clear
 Packaging: Giftbox with eurolock
 Brand name: Nedis



Quantity	LxWxH (mm)	Weight
1	65x65x130	80 gr.
50	355x280x355	4540 gr.

Wi-Fi Smart LED Filament Bulb | E27 | A60 | 5 W | 500 lm | Clear

the convenience of remote control and scheduling

- Dimmable bulb in classic style - for an elegant smart home
- Pair with other bulbs and products from the Nedis® SmartLife range - to create ambient scenes
- Control via your smartphone or tablet - or with your voice if using Amazon Alexa or Google Home

Specifications

Operating temperature:	-20 - 45 °C
Antenna gain:	2.5 dBi
Max. radio transmit power:	17.5 dBm
Frequency range:	2400 - 2483.5 MHz
Colour rendering index (Ra):	80
Overall length:	110 mm
Colour temperature:	2700 K
Diameter:	60 mm
Programming functions:	Switch On
Programming functions:	Switch Off
Programming functions:	Dimmable
Programming functions:	Switch On with Time Delay
Programming functions:	Switch Off with Time Delay
App available for:	Android™ & iOS
Compatible with smarthome:	Nedis® SmartLife
Input voltage:	230 VAC 50 Hz
Wattage:	5 W
Rated luminous flux:	500 lm
Rated life time of lamp:	20000 h
Material:	Glass
Colour:	Transparent
Lamp shape:	A60
Energy class:	A+
Lamp finish:	Clear
Dimmable:	Yes
Energy consumption per 1000 h:	5 kWh
Wattage equivalent:	40 W
Wireless technology:	Wi-Fi
Technology:	Filament LED
Base:	E27
Light colour:	Dimmable White



Wi-Fi Smart LED Filament Bulb | E27 | A60 | 5 W | 500 lm | Clear

Light colour: Warm White

Package contents

Smart bulb
Quick start guide