

SHARK 315W

Gel insulated join



Product illustrations are exemplary and may differ from the chosen product. Further variants and individual customization, we will gladly provide you on request.



Material	Polyamide
Filling	Silicone
Temp. range min	-20 °C
Temp. range max	90 °C
Glow wire test	self-extinguishing
Voltage	0,6 kV - 1 kV
Quantity of cable	3
Order no. UK	SH0315W
Type	SHARK 315W
Packing unit	1
ETIM-Classification	EC001169

Remarks:

Ampere: 5

Cable Size: 3 core

LxBxH: 40x72x23 mm

Description:

SHARK SMARTSHARK Pre-filled gel insulated straight joint. Includes 3 pole terminal block.

Additional Info:

Ready to use, re-enterable, no mixing or pouring, immediate operation, excellent electrical insulation, good mechanical strength, no expiry date.

21.03.2019

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

☎ +44-12-08816062 · 📠 +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk