

SHARK 6801 BW

SHARK SIXEIGHT



Product illustrations are exemplary and may differ from the chosen product. Further variants and individual customization, we will gladly provide you on request.

Material	Polyamide
Filling	Silicone
Temp. range min	-20 °C
Temp. range max	90 °C
Glow wire test	self-extinguishing
Protection class	IP68
Voltage	0,6 kV - 1 kV
Order no. UK	SH6801BW
Type	SHARK 6801 BW
Packing unit	1
ETIM-Classification	EC001169

Remarks:

Ampere: 32
Cable Size: (3 core) 2.5 - 6 mm
LxBxH: 190x60x48 mm

Description:

SHARK SIXEIGHT IP 68 rated pre-filled gel insulated joint, including modular bolts and gaskets, constant force role springs and earthing braid.

Additional Info:

Ready to use, re-enterable, 100% watertight, 100% dust-tight, suitable for SWA cables, no mixing or pouring, immediate operation, excellent electrical insulation, good mechanical strenght, no expiry date.

21.03.2019

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

☎ +44-12-08816062 · 📠 +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk