

TKE/P 25/FFD/02/2.5



Product illustrations are exemplary and may differ from the chosen product. Further variants and individual customization, we will gladly provide you on request.

Material cable gland	Polyamide
Material sealing gasket	EPDM
Temp. range min	-40 °C
Temp. range max	100 °C
Protection class	IP66
Product Color	RAL 7035
Thread type	M
Ø Connection thread D	25
Lead	1,5
Length screw-in thread L	10 mm
Key width SW	29 mm
Total length TL	38 mm - 47 mm
Glow wire test	750 °C
Type of cable anchorage	A
Install. torques fitting	10 N/m
Install. torques cap nut	4 N/m
Impact category	4
Order no. RAL 7035	10106241
Type	TKE/P 25/FFD/02/2.5
Packing unit	1

Description:

IP 68 Plastic cable gland for flat cable insert. ESKV 25/ FFD for 2 x 2.5 mm twin and earth. Kit contains insert, and locknut.

19.03.2019

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

☎ +44-12-08816062 · 📠 +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk