

# WTHA 1

Hot Air Station 900 W  
Product no.: T0053173399



## Benefits

- › 900 W Hot air station for simple repair and heating tasks
- › Modern and intuitive operational concept thanks to clear menu structure
- › Reduced footprint thanks to stackability
- › Electronical controlled temperature
- › Accurate adjustment of hot air through brushless turbine
- › Up to 5 pre-sets which can be automatically run in a profile
- › Housing cover useable as storage
- › OFF time, Prozess window, Lock function, Offset
- › Unit inkl. safety rest and fixed hot air iron



### Technical Data

Dimensions L x W x H (mm)	212 x 172 x 122 mm
Dimensions L x W x H (inches)	8,35 x 6,77 x 4,80 Inch
Weight (approx.) in kg	1,95 kg
Voltage	230 V
Power	900 W
Channels	1
Temperature range (depends on tool) °C	50 - 600
Temperature range (depends on tool) °F	100 - 1000
Temperature accuracy °C	± 30
Temperature accuracy °F	± 54
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	Via 3,5 mm pawl socket on front of device
Display	Graphical backlit LC-Display
Air consumption l/min	---
Operating pressure in bar/psi	Na
Capacity l/min	5 - 60 l / 20°C 5 - 110 l / 300°C
Vacuum	Na