

WX 1011 SOLDER STATION WXMP 230V UK F/G



Benefits



For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning



Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	170 x 151 x 130
Dimensions L x W x H (inches)	6, 69 x 5, 94 x 5, 12
Weight (approx.) in kg	3.2
Voltage	230 V
Power	200 W
Channels	1
Temperature range (depends on tool) °C	100 - 550
Temperature range (depends on tool) °F	200 - 999
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding socket	Via 3, 5 mm pawl socket on back of device
Display	255 x 128 dots / Backlighting
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	---
Vacuum	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE