





**MICRO PUSH-WIRE CONNECTOR
FOR JUNCTION BOXES 4-
CONDUCTOR TERMINAL BLOCK
PUSH-WIRE® CONNECTION
243-504**

ITEM-NO. (ITEM-NO.)	243-504
DIAMETER1 (DIAMETER / mm)	4 x 0.6 - 0.8
DIAMETER2 (DIAMETER / AWG)	22 - 20
Strip length (Strip length / mm)	5 - 6
Measured voltage (Measured voltage / V)	100
Measured shock voltage (Measured shock voltage / kV)	1.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	6
P (NO. OF POLES)	4
Height (Height / mm)	6.8
Width (Width / mm)	10
Depth (Depth / mm)	10
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	1
COLOR (COLOR)	gelb
WEIGHT (WEIGHT / g)	0.76