

Mini installation beacon / MC55

## MC55 UL Beacon 10-30V RGB M12





| MECHANICAL DATA             |                   |  |
|-----------------------------|-------------------|--|
| Height                      | 71 mm             |  |
| Diameter                    | 55 mm             |  |
| Materials                   | PC                |  |
| Dome colour                 | Tranclucent       |  |
| Housing colour              | Black             |  |
| Protection category         | IP69K             |  |
| Connection                  | M12 plug 5-pole   |  |
| Type of fixing              | Built-in mounting |  |
| Working temperature minimum | -20°C             |  |
| Working temperature maximum | +50°C             |  |
| Weight with packaging       | 93 g              |  |
| Product weight              | 66 g              |  |

| ELECTRICAL DATA             |                           |
|-----------------------------|---------------------------|
| Operating voltage           | 10-30V                    |
| Operating voltage type      | DC                        |
| Operating voltage tolerance | +/- 0%                    |
| Rated operational voltage   | 24 VDC                    |
| Rated operational current   | 120 mA                    |
| Rated inrush current        | <700mA                    |
| Protection class            | Protection class 2        |
| Pollution degree            | 3                         |
|                             | In the connection area: 2 |
| Overvoltage category        | I                         |
| Isolation voltage           | Ui = 50V / Uimp = 330V    |

| OPTICAL DATA         |                  |
|----------------------|------------------|
| Light source         | LED              |
| Light colour         | MC 7 colours     |
| Optical signal image | Permanent        |
| Service life optical | 50,000 h maximum |

| APPROVAL DATA     |         |
|-------------------|---------|
| Conforms with CE  | Yes     |
| WEEE              | Yes     |
| Conforms with CCC | No      |
| Conforms with UL  | cULus   |
| UL Type Rating    | Type 4X |
| Conforms with FCC | No      |


For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.


Mini installation beacon / MC55

## MC55 UL Beacon 10-30V RGB M12

| Conforms with IC              | No                    |
|-------------------------------|-----------------------|
| EAC certificate available     | No                    |
| Conforms with UKCA (Importer) | Yes (WERMA (UK) Ltd.) |
| Conforms with AS-I            | No                    |
| Conforms with DNV             | No                    |
| Conforms with RoHS CN         | 25 years              |
| Conforms with VdS             | No                    |
| MTTF-value [years]            | 133                   |

## **DRAWING**





For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.