

KombiSIGN 40 / ClassicLOOK

## Terminal element USB BK



|                  |                     |
|------------------|---------------------|
| <b>Part No.:</b> | <b>631.810.53</b>   |
| <b>Series:</b>   | <b>KombiSIGN 40</b> |



### MECHANICAL DATA

|                             |                  |
|-----------------------------|------------------|
| Height                      | 59 mm            |
| Diameter                    | 40 mm            |
| Materials                   | PC               |
| Dome colour                 | Black            |
| Protection category         | IP66<br>IP69K    |
| Connection                  | USB              |
| Tension relief              | Not present      |
| Type of fixing              | Adapter required |
| Working temperature minimum | -30°C            |
| Working temperature maximum | +60°C            |
| Weight with packaging       | 49 g             |
| Product weight              | 35 g             |

### ELECTRICAL DATA

|                             |                    |
|-----------------------------|--------------------|
| Operating voltage           | 5V (USB)           |
| Operating voltage type      | DC                 |
| Operating voltage tolerance | +/- 0%             |
| Rated operational voltage   | 5 VDC              |
| Rated operational current   | 500 mA             |
| Protection class            | Protection class 3 |
| Pollution degree            | 3                  |
| Request to external PSU     | SELV/PELV          |
| Current carrying capacity   | 90 mA              |
| connectivity                | USB                |

### APPROVAL DATA

|                               |                       |
|-------------------------------|-----------------------|
| Conforms with CE              | Yes                   |
| Conforms with RoHS directive  | Yes                   |
| WEEE                          | Yes                   |
| Conforms with ATEX-directive  | No                    |
| Conforms with CCC-Ex          | No                    |
| Conforms with CCC             | No                    |
| Conforms with UL              | cULus                 |
| UL Type Rating                | Type 12               |
| Conforms with FCC             | No                    |
| Conforms with IC              | No                    |
| EAC certificate available     | Yes                   |
| Conforms with UKCA (Importer) | Yes (WERMA (UK) Ltd.) |



For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.

KombiSIGN 40 / ClassicLOOK

## Terminal element **USB BK**

|                       |    |
|-----------------------|----|
| Conforms with CMIM    | No |
| Conforms with AS-I    | No |
| Conforms with DNV     | No |
| Conforms with RoHS CN | No |
| Conforms with VdS     | No |



For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.