

Permanent Light 216 / Bulb

## Bulb 7W BA15D 12V



**Part No.:** 955.015.34

### MECHANICAL DATA

Height	54 mm
Diameter	16 mm
Housing colour	Silver
Weight with packaging	10 g
Product weight	8 g

### ELECTRICAL DATA

Operating voltage	12V
Operating voltage frequency	50Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	12 VDC
Rated operational current	583 mA
Rated inrush current	5.830 mA
Power illuminant	7 W

### OPTICAL DATA

Lamp fitting/socket	BA15d
---------------------	-------

### APPROVAL DATA

Conforms with CE	No
Conforms with RoHS directive	Fulfills substance restriction
WEEE	No
Conforms with ATEX-directive	No
Conforms with CCC	No
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	No
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No



For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.