

## Permanent Light 815 / Bulb Bulb 7W BA15D 48V



**Part No.:** 955.015.36

### MECHANICAL DATA

Height	54 mm
Diameter	16 mm
Housing colour	Silver
Weight with packaging	9 g
Product weight	9 g

### ELECTRICAL DATA

Operating voltage	48V
Operating voltage frequency	50Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	48 VAC
Rated operational current	146 mA
Rated inrush current	1.460 mA
Power illuminant	7 W

### OPTICAL DATA

Lamp fitting/socket	BA15d
---------------------	-------

### APPROVAL DATA

Conforms with CE	No
Conforms with RoHS directive	Fulfills substance restriction
WEEE	No
Conforms with ATEX-directive	No
Conforms with CCC	No
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	No
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No



For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.