

Permanent Light 815 / Bulb Bulb 7W BA15D 115V



Part No.: 955.015.37

MECHANICAL DATA

Height	54 mm
Diameter	16 mm
Housing colour	Silver
Weight with packaging	9 g
Product weight	9 g

ELECTRICAL DATA

Operating voltage	115V
Operating voltage frequency	60Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	115 VAC
Rated operational current	61 mA
Rated inrush current	610 mA
Power illuminant	7 W

OPTICAL DATA

Lamp fitting/socket	BA15d
---------------------	-------

APPROVAL DATA

Conforms with CE	No
Conforms with RoHS directive	Fulfills substance restriction
WEEE	No
Conforms with ATEX-directive	No
Conforms with CCC	No
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	No
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.