

Accessories / LED Bulb

LED Bulb 24VAC/DC Ø45x80



Part No.: 956.050.75

MECHANICAL DATA

Height	80 mm
Diameter	45 mm
Weight with packaging	28 g
Product weight	22 g

ELECTRICAL DATA

Operating voltage	12-24V
Operating voltage type	AC/DC
Operating voltage frequency	50Hz
Operating voltage tolerance	+/- 10%
Rated operational voltage	24 VDC
Rated operational current	250 mA
Rated inrush current	3 A
Power illuminant	3 W

OPTICAL DATA

Light source	LED
Light colour	White
Optical signal image	Permanent
Lamp fitting/socket	E27

APPROVAL DATA

Conforms with CE	No
Conforms with RoHS directive	Fulfills substance restriction
WEEE	No
Conforms with ATEX-directive	No
Conforms with CCC-Ex	No
Conforms with CCC	No
Conforms with UL	No
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	No
Conforms with UKCA (Importer)	No
Conforms with CMIM	No
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No
Conforms with VdS	No



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.