

Wiha FlipSelector and XLSelector.

Couldn't be smaller!



The Wiha FlipSelector: simplest handling guaranteed.

As the successor of the XSelector, the FlipSelector also features compactness, but combines it with even easier handling and 2 additional bit slots.

Now with 12 bits, the configuration variants can be ideally adapted to individual types of applications.

Simply slide the Wiha logo down and the bit clamping element pivots by 180° and releases the bits for removal.

The XLSelector is perfect for those who need more than 12 bits. It holds 30 bits and thus covers an extremely broad fastening spectrum. Thanks to its super-flat design, it fits easily into any electrical toolbox.



Always ready to hand, without annoying searching.



Because it is extremely flat and compact, the XLSelector fits into any case



Wiha FlipSelector

- Contains 12 bits and a bit holder
- Bit box made of impact-resistant polyamide – permanently robust
- Effortless handling, opens at the press of a button
- At 99 x 63 x 17 mm, it fits into any shirt or trouser pocket
- Optional belt clip available to facilitate work further



Wiha XLSelector

- Extremely flat and compact bit box containing 30 bits and a bit holder
- Simple removal of the clearly arranged bits
- At 135x80x17.5 mm, there is space for the XLSelector even in fully packed electrical toolboxes

Wiha XLSelector.

Couldn't be smaller!

XSelector sales counter display.



7948 VB1 XLSelector display.
Acryl glass display with 6 pieces.

Size: 25 x 12 x 34 cm (WxDxH)

Order-No.	Series				
29541	7948 VB1				1
	① 7010 Z	1x4.5	1x5.5	1x6.5	
	⊕ 7011 Z	2xPH1	4xPH2	1xPH3	
	⊕ 7012 Z	2xPZ1	5xPZ2	1xPZ3	
	⊕ 7015 Z	2xT10	2xT15	2xT20	3xT25
		2xT30	1xT40		
	7113 S	1xUniversal holder 58 mm magnetic			



7948 VB2 XLSelector display.
Acryl glass display with 6 pieces.

Order-No.	Series				
36165	7948 VB2				1
	⊕ 7012 HOT	3xPZ1	10xPZ2	2xPZ3	
	⊕ 7015 Z	2xT10	2xT15	3xT20	4xT25
		2xT30	2xT40		
	7113 S	1xUniversal holder 58 mm magnetic			



7948 VB3 XLSelector display.
Acryl glass display with 6 pieces.

Order-No.	Series				
36166	7948 VB3				1
	⊕ 7041 ZOT	1xPH1	1xPH2	1xPH3	
	⊕ 7042 ZOT	1xPZ1	1xPZ2	1xPZ3	
	⊕ 7045 Z	1xT10	1xT15	1xT20	1xT25
		1xT30	1xT40		
	7148C	1xCentroFix quick release holder style E 6.3			

XLSelector with bit ratchet.



7948-043 XLSelector Torsion, mixed, with 1/4" bit ratchet, 17-pcs.

Housing: Box made of high quality plastic.
Contains 15 bits, bitholder and bit ratchet.

Bits: 25 mm Z and ZOT bits.

Geometry: Patented torsion zone to prevent premature breaking of the bit when under stress.

Bit holder: 1/4" universal holder, magnetic.

Application: Universal assortment for all types of fastening in trade and industry.
More applications with practical bit ratchet.

Extra: 1/4" universal holder can be used as an extension.

Order-No.	Series				
36951	7948-043				5
	⊕ 7011 ZOT	1xPH1	1xPH2		
	⊕ 7012 ZOT	1xPZ1	1xPZ2	1xPZ3	
	⊕ 7013 Z	1x3.0	1x4.0	1x5.0	1x6.0
	⊕ 7015 ZOT	1xT10	1xT15	1xT20	1xT25
		1xT30	1xT40		
	7113 S	1xUniversal holder 58 mm, magnetic			
	SB 2463 001	1x1/4" bit ratchet, with thumb wheel			



7948 VB4 XLSelector with bit ratchet, display, 6-pcs.
Acryl glass display with 6 pieces.

Order-No.	Series				
36929	7948 VB4				1
	⊕ 7011 ZOT	1xPH1	1xPH2		
	⊕ 7012 ZOT	1xPZ1	1xPZ2	1xPZ3	
	⊕ 7013 Z	1x3.0	1x4.0	1x5.0	1x6.0
	⊕ 7015 ZOT	1xT10	1xT15	1xT20	1xT25
		1xT30	1xT40		
	7113 S	1xUniversal holder 58 mm magnetic			
	SB 2463 001	1x1/4" bit ratchet with thumb wheel			