

# Product datasheet

Specifications



## Easy UPS battery module, 24V DC-DC, DIN Rail, Industrial, 4.5Ah



XB005XPDR

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage 24 V DC

Main Output Voltage 24 V DC

Battery type VRLA

Provided equipment User manual

### Batteries & Runtime

Battery location Battery cabinet

Device mounting DIN rail

Battery voltage 24 V

### Physical

Colour Metal grey

Height 129 mm

Width 192 mm

Depth 119 mm

Net weight 4.5 kg

Mounting preference No preference

USB compatible No

### Output

Battery capacity 4.5 Ah

### Conformance

Product certifications CE  
TÜV

Standards IEC 62368-1

## Environmental

Ambient air temperature for operation	-15...50 °C
Operating altitude	0...3000 m
Relative humidity	0...95 %
Ambient air temperature for storage	-15...70 °C
Storage altitude	0...3000 m
Storage Relative Humidity	0...95 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	234.7 mm
Package 1 Width	190 mm
Package 1 Length	188 mm
Package 1 Weight	4.8 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
RoHS exemption information	Yes
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	1 Year
----------	--------

## Recommended replacement(s)