



## Main

Range of product	Harmony XB5
Bezel material	Dark grey plastic
Product or component type	Hour counter
Mounting diameter	22 Mm
Reset	Without

## Complementary

[Us] rated supply voltage	12...24 V +/- 10 %
Display digits	5
Current consumption	7...15 mA
Resistance to high pressure washer	7000000 Pa at 55 °C, distance : 0.1 m
Mounting mode	Flush-mounted
Mounting support	Panel mounting
Height	30 Mm
Width	30 Mm
Depth	60 Mm
Device presentation	Monolithic product
Net weight	0.045 Kg

## Environment

Protective treatment	TH
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Electrical shock protection class	Class II conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 13 NEMA 4X
Standards	EN 60947-5-1
Product certifications	CE UL

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	46.0 G
Package 1 Height	3.4 Cm
Package 1 width	5.4 Cm
Package 1 Length	8.6 Cm
Unit Type of Package 2	S03
Number of Units in Package 2	100
Package 2 Weight	5.074 Kg
Package 2 Height	30 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm
Package 3 Height	30 Cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**