îiyama

iiyama ProLite XU2792UHSU-B1 LED display 68.6 cm (27") 3840 x 2160 pixels 4K Ultra HD Black

Product name: XU2792UHSU-

В1

iiyama ProLite XU2792UHSU-B1. Display diagonal: 68.6 cm (27"), Display resolution: 3840 x 2160 pixels, HD type: 4K Ultra HD, Display technology: LED, Display surface: Matt, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting. Product colour: Black







Display		Ports & interfaces	
Display diagonal * Display brightness (typical) Display resolution * Native aspect ratio * Response time HD type * Display technology *	ess (typical) 300 cd/m² on * 3840 x 2160 pixels atio * 16:9 4 ms 4K Ultra HD	DisplayPorts quantity Audio input Headphone out * Headphone outputs Headphone connectivity HDCP AC (power) in	1 X ✓ 1 3.5 mm ✓
Display surface	Matt	Ergonomics	
Screen shape * Supported graphics resolutions Contrast ratio (typical) * Contrast ratio (dynamic) Viewing angle, horizontal Viewing angle, vertical Display number of colours * Panel type * Pixel pitch Horizontal scan range Vertical scan range Viewable size, horizontal Viewable size, vertical Viewable size diagonal	Matt Flat 3840 x 2160 1000:1 80000000:1 178° 1.073 billion colours IPS 0.16 x 0.16 mm 31 - 90 kHz 55 - 75 Hz 59.6 cm 33.5 cm 68.4 cm	Panel mounting interface Cable lock slot * Cable lock slot type VESA mounting * Height adjustment * Tiltable Tilt angle range Picture-in-Picture On Screen Display (OSD) On Screen Display (OSD) languages Number of OSD languages Power	100 x 100 mm ✓ Kensington ✓ X ✓ -5 - 22° ✓ Czech, German, Dutch, English, Spanish, French, Italian, Japanese, Polish, Russian 10
Performance		Energy efficiency class (SDR) *	G
NVIDIA G-SYNC * AMD FreeSync * Flicker-free technology Low Blue Light technology Multimedia Built-in speaker(s) * Number of speakers	X X ✓ ✓ ✓	Energy consumption (SDR) per 1000 hours * Power consumption (typical) * Power consumption (standby) * Power consumption (off) AC input voltage AC input frequency	32 kWh 34 W 0.5 W 0.5 W 100 - 240 V 50/60 Hz
RMS rated power Built-in camera *	4 W	Input current Energy efficiency scale	1.5 A A to G

Design		Operational conditions	
Market positioning * Product colour * Feet colour Certification	Graphics design Black Black TCO, CE, TÜV-GS, EAC, PSE REACH	Operating temperature (T-T) Storage temperature (T-T) Operating relative humidity (H-H) Storage relative humidity (H-H)	5 - 35 °C -20 - 60 °C 10 - 80% 5 - 85%
Ports & interfaces		Weight & dimensions	
Built-in USB hub * USB hub version USB upstream port type Number of upstream ports USB Type-A downstream ports quantity DVI port	3.2 Gen 1 (3.1 Gen 1) USB Type-B 1	Width (with stand) Depth (with stand) Height (with stand) Weight (with stand) Width (without stand) Depth (without stand) Height (without stand)	613.5 mm 197 mm 440.5 mm 4.6 kg 61.4 cm 5.4 cm 37 cm
DVI-D ports quantity HDMI * HDMI ports quantity	1 v 1	Packaging data Stand included Cables included	✓ AC, DisplayPort, HDMI, USB



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.