





All trademarks and registered marks are the property of their respective companies. Errors excepted. Subject to change without prior notice. Images may differ from original product.



We are entering our Advanced + series with the XILENT BREEZE Performance A + X7 PC case. The Case offers numerous possibilities to set up the interior individually and easily. In addition, you have a crystal-clear view inside to your components because of the tempered glass side panel. With the three ARGB fans on the front panel and the full diamond mesh front, it is not only visually impressive, but also proves to be a true performance monster!

Highlights

- Full Diamond Mesh Front with three ARGB Xilence Fans and a black 120mm PWM Fan in rear preinstalled
- No visible screws at the tempered glass side panel, because of the connection from the back
- With 220 mm width offers the case more space for a excellent air circulation
- Suitable for liquidcoolers with 360mm, 280mm und 240mm radiators in the front 280mm oder 240mm radiators on top or a 120mm radiator in the rear
- Space for Graphiccards with a length up to 350mm and CPU-Coolers with a height up to 165mm
- Xilence tool-free Graphiccard Mounting
- There is up to 25 mm space behind the mainboard for individually cable management
- Tool-free installation for HDD / ODD
- For better ventilation in the case, there is a PSU shroud at the bottom
- Efficient, easily removable and easy-to-clean dust filters at the top and back
- 2xUSB 3.0 Ports at Top-Panel

Design

- Unique diamond front panel design
- Snap-in front panel for easy PC assembly
- Black housing with tempered glass side-panel for a classy look

Service

- Two years warranty

- Developed, designed and quality controll in Germany



All trademarks and registered marks are the property of their respective companies. Errors excepted. Subject to change without prior notice. Images may differ from original product.



Specifications


Case Typ	Midi Tower
Case Dimensions (L x B x H in mm)	370 x 220 x 470mm
Metal Structure Dimensions (L x B x H in mm)	410 x 220 x 470mm with Front-Panel
Package Dimensions (L x B x H in mm)	521 x 279 x 486mm
Mainboard-Compatibility	ATX, micro-ATX, mini-ITX
Formfactor PSU	ATX (not included)
Case Material	Steel (SPCC),
Material Front Panel	ABS-Plastic
Material Side Panel	tempered Glass
Multi-Media I/O-ports	2 x USB 3.0, HD Audio (Microphone + Audio)
PCI slots	7 + 2 extension slots
Drive Capacity:	2.5" x 4 +3.5" x 2 or 2,5" x 6
Cooling Fan Support (mm)	Front:3x 120mm 3x140mm 2x200mmTop:2 x 120mm / 2x140mmRear:1 x 120mmBottom:up to 2 x 120mm
Radiator Support (mm)	Front: 360mm/ 280mm/ 240mm Top: 280mm/240mm Rear: 120mm
Hardware Dimensions (mm)	Cooler height:165mmGPU length:up to 350mmPSU length:200mm
SSD	up to 4 x
Weight (kg)	6.70 kg (Net), 7.70 kg (Gros)



All trademarks and registered marks are the property of their respective companies. Errors excepted. Subject to change without prior notice. Images may differ from original product.



Maximum Dimensions





All trademarks and registered marks are the property of their respective companies. Errors excepted. Subject to change without prior notice. Images may differ from original product.





25 mm space for individually cable management




All trademarks and registered marks are the property of their respective companies. Errors excepted. Subject to change without prior notice. Images may differ from original product.



Top & Front-Panel

CCE Rohs









Logistische Daten

Manufacturer number Article number EAN Barcode X712.RGB XG131 4044953503016

All trademarks and registered marks are the property of their respective companies. Errors excepted. Subject to change without prior notice. Images may differ from original product.