

Performance C Series

Fans 80mm/92mm/120mm/140mm

The Xilence Performance C Series excels with an extraodinary price-performance ratio and a very good proficency combined with a low noise developement. The black and red case fans, all equipped with a hydro bearing are available in three different sizes.



Product Features

- optimal performance in every situation
- hydro bearing fan

Fan Speed

Fan Speed

- airflow-optimized rotor blades

Technical Data

Fan Dimensions	80 x 80 x 25mm
Connector Type	small 3 Pin & BIG 4 Pir
Noise Level	17 dB (A)
PWM	no
Fan Bearing	hydro bearing
Air Flow	18.61 CFM

 $1.500 \text{ RPM} \pm 10\%$

140mm

80mm

Fan Dimensions 140 x 140 x 25mm small 3 Pin & BIG 4 Pin Connector Type 20 dB (A) Noise Level

PWM nο Fan Bearing hydro bearing 41.37 CM Air Flow

92mm

92 x 92 x 25mm small 3 Pin & BIG 4 Pin 21 dB (A) hydro bearing 27.45 CFM $1.500 \text{ RPM} \pm 10\%$

120mm

120 x 120 x 25mm small 3 Pin & BIG 4 Pin 26 dB (A) hydro bearing 44.71 CFM $1.300 \text{ RPM} \pm 10\%$

Logistical Data

Manufacturer Number XPF92.R XPF120.R XPF140.R XPF80.R Item Number XF037 XF038 XF039 XF050 **EAN Barcode** 4044953500879 4044953501135 4044953500855 4044953500862















900 RPM ± 10%