

DTS32Z19R [V001] ✓ ACTIVE

DEUTSCH | DEUTSCH 38999 Metal Covers

TE Internal #: YDTS32Z19RV0010000

DEUTSCH 38999 Metal Covers, Circular Connector Caps & Covers, Protective Cover, Size 19, Wire Rope with PTFE Coating, Sealable

[View on TE.com >](#)



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Protective Cover**

Compatible With Circular Connector Shell Size: **19**

Cap to Flange Attachment: **Wire Rope with PTFE Coating**

Sealable: **Yes**

Operating Temperature Range: **-65 – 175 °C [-85 – 347 °F]**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Protective Cover
Sealable	Yes

Body Features

Sealing Cap Plating Material	Black Zinc-Nickel Alloy
Sealing Cap Material	Aluminum
Cap Material	Metal
Sealing Gasket Material	Silicone

Mechanical Attachment

Cap to Flange Attachment	Wire Rope with PTFE Coating
--------------------------	-----------------------------

Dimensions

Length	127 mm[5 in]
--------	--------------

Usage Conditions

Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]
-----------------------------	----------------------------

Operation/Application

Compatible With Circular Connector Shell Size	19
---	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D38999-DTS19C
Straight Plug: D38999, 19-35 Insert, Electroless Nickel Plating



TE Part # CAT-D38999-DTS19B
Straight Plug: D38999, 19-32 Insert, Electroless Nickel Plating



TE Part # YDTS24Z19-35PNV001
RECP ASSY



TE Part # CAT-D38999-DTS19A
Straight Plug: D38999, 19-11 Insert, Electroless Nickel Plating

Also in the Series | DEUTSCH 38999 Metal Covers



Circular Connector Caps & Covers(136)

Customers Also Bought



TE Part #YDTS26Z17-35PBV001
PLUG ASSY



TE Part #BTH3-09-04-1-ZN
BTH3-09-04-1-ZN



TE Part #BTH3-15-08-1-ZN
BTH3-15-08-1-ZN



TE Part #YDTS32Z17RV0010000
CAP ASSEMBLY



TE Part #YDTS32Z23RV0010000
CAP ASSEMBLY



TE Part #ZPF000000000167219
DTS 24 B 09-35 PA



TE Part #ZPF000000000167220
DTS 24 B 09-35 PN



TE Part #ZPF000000000200580
DTS 24 B 11-35 PN



TE Part #ZPF000000000203712
DTS 24 B 17-35 SN



TE Part #ZPF000000000167319
DTS 26 B 17-35 PN

Documents

Product Drawings

CAP ASSEMBLY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_YDTS32Z19RV0010000_2.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_YDTS32Z19RV0010000_2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDTS32Z19RV0010000_2.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS](#)

English