

# ZCE01

limit switch head ZCE - without lever - spring  
return - left and right actuation



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Rotary head
Product compatibility	XCKD XCMD XCKP XCKT
Associated lever	ZCY25 ZCY19 ZCY46 ZCY45 ZCY59 ZCY23 ZCY55 ZCY22 ZCY48 ZCY53 ZCY54 ZCY39 ZCY49 ZCY18 ZCY69 ZCY91 ZCY26 ZCY12 ZCY44 ZCY15 ZCY16 ZCY17 ZCY81
Associated body	ZCD31 ZCMD29L2 ZCMD39L5 ZCT21N12 ZCP29M12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCMD37L2  
 ZCP21M12  
 ZCMD61C12  
 ZCT25P16  
 ZCMD29L5  
 ZCT27N12  
 ZCT28G11  
 ZCP29  
 ZCD35  
 ZCMD21L5  
 ZCD25  
 ZCT21G11  
 ZCMD37L5  
 ZCMD41L2  
 ZCD27  
 ZCMD25L1  
 ZCD21M12  
 ZCP28  
 ZCMD81L5  
 ZCT25N12  
 ZCMD39L1  
 ZCP25  
 ZCMD37L1  
 ZCMD21L08U78  
 ZCMD69C12  
 ZCMD21C12  
 ZCMD25L5  
 ZCMD29C12  
 ZCT27P16  
 ZCMD29L1  
 ZCD21  
 ZCT28N12  
 ZCT26G11  
 ZCP31  
 ZCT26P16  
 ZCT26N12  
 ZCMD25L2  
 ZCMD21M12  
 ZCD29M12  
 ZCD28  
 ZCP21  
 ZCMD41L1  
 ZCMD81L2  
 ZCT27G11  
 ZCD39  
 ZCP26  
 ZCMD61M12  
 ZCD37  
 ZCMD81L1  
 ZCMD21L08R12  
 ZCP35  
 ZCP37  
 ZCMD21L1  
 ZCT28P16  
 ZCMD39L2  
 ZCMD21L2  
 ZCT21P16  
 ZCP27  
 ZCP39  
 ZCD26  
 ZCT25G11  
 ZCD29  
 ZCMD41L5

Movement of operating head	Rotary
Type of operator	Without operating lever spring return metal
Type of approach	Lateral approach 2 directions

### Complementary

Positive opening	With
Device presentation	Basic element
Compatibility code	ZCE

## Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------