

**Z-series  
ZQV 2.5N/2 BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

|            |                                            |
|------------|--------------------------------------------|
| Type       | ZQV 2.5N/2 BL                              |
| Order No.  | <a href="#">1527740000</a>                 |
| Version    | Z-series, Cross-connector, No. of poles: 2 |
| GTIN (EAN) | 4050118448658                              |
| Qty.       | 60 pc(s).                                  |

**Z-series  
ZQV 2.5N/2 BL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 7.9 mm  | Width (inches)  | 0.311 inch |
| Height     | 24.7 mm | Height (inches) | 0.972 inch |
| Depth      | 2.8 mm  | Depth (inches)  | 0.11 inch  |
| Net weight | 1.124 g |                 |            |

**Material data**

|                           |       |        |      |
|---------------------------|-------|--------|------|
| Material                  | Wemid | Colour | Blue |
| UL 94 flammability rating | V-0   |        |      |

**Additional technical data**

|                          |                 |                |         |
|--------------------------|-----------------|----------------|---------|
| Explosion-tested version | Yes             | Type of fixing | Plugged |
| Type of mounting         | Direct mounting |                |         |

**Dimensions**

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 5.1 mm |
|-----------------|--------|

**Rating data**

|               |      |
|---------------|------|
| Rated current | 24 A |
|---------------|------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 6.0   | EC000489    | eClass 6.2 | 27-14-11-40 |
| eClass 8.1 | 27-14-11-40 | eClass 9.0 | 27-14-11-40 |
| eClass 9.1 | 27-14-11-40 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |                                                    |
|--------------------|----------------------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 1 TERM 16/17 EN</a>                |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>           |
| User Documentation | <a href="#">2434520000_BED-ANL.ZQV_A_REIHE.pdf</a> |