

**Z-series**  
**ZQV 1.5N/10 RD****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

Type	ZQV 1.5N/10 RD
Order No.	<a href="#">1985800000</a>
Version	Z-series, Cross-connector, No. of poles: 10
GTIN (EAN)	4050118370393
Qty.	20 pc(s).

## Data sheet

### Z-series ZQV 1.5N/10 RD

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	33.5 mm	Width (inches)	1.319 inch
Height	21.9 mm	Height (inches)	0.862 inch
Depth	2.8 mm	Depth (inches)	0.11 inch
Net weight	3.391 g		

### Material data

Material	Wemid	Colour	Red
UL 94 flammability rating	V-0		

### Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

### Dimensions

Pitch in mm (P)	3.5 mm
-----------------	--------

### Rating data

Rated current	17.5 A
---------------	--------

### Classifications

ETIM 6.0	EC000489	eClass 6.2	27-14-11-40
eClass 9.1	27-14-11-40		

### Downloads

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">2434520000_BED-ANL.ZQV_A_REIHE.pdf</a>