

Secvest Wireless Retrofit Kit for FOS 550 - AL0125 (white)

Art. no. FUFT50037W

Page 1 of 2



- Double your protection by combining mechanical security with electronic monitoring
- Active intrusion protection, thanks to simple upgrading of the mechanical system with electronics
- Even detects intrusion attempts
- Connection points for passive glass break detectors

Connecting mechanical security and electronic monitoring

At first glance, it is difficult to tell the difference between the FOS 550 window bar lock, which is purely mechanical, and the FOS 550 E wireless window bar lock, which is electronic. You can use the wireless upgrade kit to prepare the FOS 550 mechanical window bar lock for use with the Secvest wireless alarm system.

The wireless upgrade kit contains: Electronic attachment with circuit board and fasteners, batteries, FOS 550 E twist handle and magnet bracket including magnet and fasteners. Upgrading FOS 550 window bar locks that have already been installed is simple and uncomplicated and can be done at any time.

Note: We recommend the ABUS wireless test box for optimum detection of the wireless range of the mechatronic products on site.

Secvest Wireless Retrofit Kit for FOS 550 - AL0125 (white)

Art. no. FUFT50037W

Page 2 of 2

Technical Data:

Colour options	white, brown
Approval no.	M 197093
Connections	Clamping terminal
Battery type	2 x 1.5 V LR03 AAA alkaline batteries
Width	32 mm
Type of detection	Magnetic field measurement
Transmission power	10 mW
Height	50 mm
Length	170 mm
Max. battery life	2 year(s)
Max. operating temperature	55 °C
Max. sending range (outdoors)	100 m
Max. sending range (building)	30 m

Min. operating temperature	-10 °C
Modulation	FM
Installation location	Windows and French windows
Tamper monitoring	Yes
Closure number	AL0125
Sensor type	Magnetic switch and magnetic field sensor system
Voltage monitoring	Yes
DC voltage supply	3 V
Environmental class	II
Certifications	VdS