



## Wall Mount Adapter

# ADS005A,B Series



- Full-range AC input 100-240Vac, 50/60Hz
- Efficiency Level V
- Class II Double Insulation
- Class B EMI
- For any I.T.E. product (IEC 60950-1)



- Ambient Temp. 40°C max
- Auto recovery for OCP/OVP/SCP
- High Efficiency
  - No Load Power Consumption under 0.3W
  - Compliant with current ErP and DOE
- Limited Power Source (LPS)
- MTBF: 50000 Hours
- Dimension: 61.8\*25.5\*33.5(mm)



Model	Power (W)	Output Voltage (V)	Output Current (A)	Ripple	Regulation	Safety
ADS005w-x045zzz	4.995	4.5	0.01-1.11	100mV	±5%	
ADS005w-x046zzz	4.968	4.6	0.01-1.08	100mV	±5%	
ADS005w-x047zzz	4.982	4.7	0.01-1.06	100mV	±5%	
ADS005w-x048zzz	4.992	4.8	0.01-1.04	100mV	±5%	
ADS005w-x049zzz	4.9	4.9	0.01-1	100mV	±5%	
ADS005w-x050zzz	5	5	0.01-1	100mV	±5%	
ADS005w-x051zzz	4.59	5.1	0.01-0.9	100mV	±5%	
ADS005w-x052zzz	4.68	5.2	0.01-0.9	100mV	±5%	
ADS005w-x053zzz	4.77	5.3	0.01-0.9	100mV	±5%	
ADS005w-x054zzz	4.86	5.4	0.01-0.9	100mV	±5%	
ADS005w-x055zzz	4.95	5.5	0.01-0.9	100mV	±5%	
ADS005w-x056zzz	4.76	5.6	0.01-0.85	100mV	±5%	
ADS005w-x057zzz	4.845	5.7	0.01-0.85	100mV	±5%	
ADS005w-x058zzz	4.93	5.8	0.01-0.85	100mV	±5%	
ADS005w-x059zzz	4.72	5.9	0.01-0.8	100mV	±5%	
ADS005w-x060zzz	4.8	6	0.01-0.8	100mV	±5%	
ADS005w-x061zzz	4.88	6.1	0.01-0.8	100mV	±5%	
ADS005w-x062zzz	4.96	6.2	0.01-0.8	100mV	±5%	
ADS005w-x063zzz	4.725	6.3	0.01-0.75	100mV	±5%	
ADS005w-x064zzz	4.8	6.4	0.01-0.75	100mV	±5%	
ADS005w-x065zzz	4.875	6.5	0.01-0.75	100mV	±5%	

\* w denotes output connector type: A for USB, B for DC cable

\* x denotes plug type: W for US, B for Europe, D for UK, A for Australia, P for China, K for Korea, J for Japan

### Atech OEM Inc.

ADD: 7F, AAEON Building, No.43, Sec. 4, Keelung Rd., Taipei City 10607, Taiwan R.O.C.  
TEL:886-2-2377-0282 FAX:886-2-2377-0283 E-mail: marketing@atechoem.com