Laserliner® **ArcoMaster**



Digital electronic angle gauge – precise, optimal measurements into the last corner

- 1. Precisely measure inside or outside angles from 0-220°: measurements of roof angle, fitting furniture or windows at corners and edges.
- 2. Additional extensible bevel for measuring angles in difficult to reach locations.
- Robust aluminium housing
- Vertical and horizontal level vials
- An illuminated LC display on each side (front and rear) to permit work at either side.
- Both displays can be flipped at the touch of a button: FlipDisplay
- Auto shut-off function
- Auto hold: for work where the LC display is not visible.
- Angle bisection displayed at the touch of a button, even in hold mode; optimal for mitre cuts.

TECHNICAL DATA







Article no.: 075.130A 4 021563 664016 FAN-Code

ArcoMaster 40 inclusive soft bag + batteries Packing dimension (W x H x D)

460 x 310 x 130 mm PU 5

Article no.: 075.131A EAN-Code: 4 021563 666683

ArcoMaster 60 inclusive soft bag + batteries Packing dimension $(W \times H \times D)$ 650 x 310 x 130 mm PU 5



Bevel extended downward



.... or upward, as needed.



LC display on the front and rear side

Display flips 180° at the touch of a button