

CASES
1300
Case

Save as PDF



Peli protector cases - Total protection box - 1300 case



Interior dimensions:
23.3 x 17.8 x 15.5 cm (9" x 7" x 6")

Watertight, crushproof, and dust proof

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Stainless steel hardware
- Pick 'N' Pluck™ with convoluted lid foam
- Unconditionally Guaranteed



Black Silver Yellow Orange Desert_tan

Peli protector cases - Total protection box - 1300 case SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)	
27 x 24.6 x 17.4 cm (11" x 10" x 7")		23.3 x 17.8 x 15.5 cm (9" x 7" x 6")	
Lid Depth	Bottom Depth	Total Depth	
3 cm (1")	12.5 cm (4.93")	15.5 cm (6.11")	
Lid Depth	Bottom Depth	Total Depth	
3 cm (1.18")	12.5 cm (4.93")	15.5 cm (6.11")	
Weight w/Foam	Weight w/o Foam	Buoyancy Max.	
1.6 kg. (3.53 lbs)	1.4kg (3.09 lbs.)	5.6 kg (12.35 lbs.)	
Range Temperature			
-40 / 99° C (-40 / 210° F)			

1300 Case Certificates

- IP67(1 meter submersion for 30 minutes)
- Def Stan 81-41/STANAG 4280

Materials

Body	Latch	Lid O-Ring	Pins
Polypropylene	ABS	PolymerStainless Steel	
Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non-Woven PET	70 Shore Nitrile

Configuration

Cat. #	Description
1300	Peli protector cases - Total protection box - 1300 case

Peli protector cases - Total protection box - 1300 case Accessories

Cat. #	Description