




BW 30.18



- Front panel 53 x 28 mm
- Integral locking spring
- With universal connections
- Touch proof connections to VBG 4
- Mounting aperture: 50 x 25 mm

Elapsed time counters BW 30 · BG 30 for panel mounting · Alternating/Direct Current

Technical data	BW 30.18 Alternating current	BG 30.18 Direct current
Supply voltages (Please state when ordering)	230 V, 50 Hz (standard) or 115 V, 50 Hz or 24 V, 50 Hz	12–48 VDC
Special voltages	–	5–24 V, 36–120 VDC, 100–300 VDC
Other voltages	on request	on request
Special frequency	60 Hz	–
Voltage tolerance	±15%	±10%
Power consumption (real power)	0.11 W	approx. 20 mW at 12 VDC
Counter capacity	99999 h.	99999 h.
Accuracy of reading	0.01 h.	0.1 h.
Numeral height	4.4 mm	4.4 mm
Numeral colour	white, decimal figures red	white, decimal figures red
Operation indicator	fast-running wheel	LED
Permitted ambient temperature	–15°...+50°C	–10°...+50°C
Enclosure	self-extinguishing thermoplastic	
Type of connection	Universal: Screw, soldered and 6.3 x 0.8 mm AMP plug-type connections	
Type of protection (DIN EN 60529)	Front IP 54	Front IP 54
Class of protection	II (when fitted in accordance with regulations)	III (up to 48 VDC)

Accessories

Retaining clip 715.005

Order number	Version
▼ BW 30.18	Alternating current
▼ BG 30.18	Direct current
▼ Housing colour	