
HAND HELD CASES

64 Series Handy Cases

Multi-purpose snap-fit hand-held enclosures designed for quick assembly

- Moulded in high grade ABS, UL94-V0
- Snap-fit base & lid assembly, via end caps
- Battery compartment lid M3 retaining screw
- · Recesses in lid, base and end caps for membrane keypads or overlays
- PCB pillars in lid and base
- · Optional EPDM gasket for IP65 seal







TYPE NO.	COLOUR	DESCRIPTION
CHH64E1BL	Blue - RAL 5007	to fit 20mm high cases
CHH64E1GR	Green - RAL 6026	to fit 20mm high cases
CHH64E1RD	Red - RAL 3020	to fit 20mm high cases
CHH64E1OR	Orange - RAL 2003	to fit 20mm high cases
CHH64E1BK	Black - RAL 9004	to fit 20mm high cases
CHH64E1YL	Yellow - RAL 1021	to fit 20mm high cases
CHH64E1DG	Grey- RAL 7001	to fit 20mm high cases
CHH64E2BL	Blue RAL 5007	to fit 30mm high cases
CHH64E2GR	Green - RAL 6026	to fit 30mm high cases
CHH64E2RD	Red - RAL 3020	to fit 30mm high cases
CHH64E2OR	Orange - RAL 2003	to fit 30mm high cases
CHH64E2BK	Black - RAL 9004	to fit 30mm high cases
CHH64E2YL	Yellow - RAL 1021	to fit 30mm high cases
CHH64E2DG	Grey- RAL 7001	to fit 30mm high cases

SPECIFICATION				
Material		Lid & base high grade ABS,UL94-V0		
Operating Temperature		Resistant to temperatures of up to 85°C		
Protection class		IP62 as standard		
		IP65 with gasket option		
Standard colours		Lid & base light grey similar to RAL 7035, end panels grey similar to RAL 7001 Lid & base dark grey similar to RAL 7021, end panels black similar to RAL 9004 Custom colours available to order		
Standard unit includes	20mm high 30mm high	Lid, base & end caps Lid, base & end caps Battery compartment & retaining screw		
Options		IP65 gasket		

BLACK	LIGHT GREY	LENGTH	WIDTH	HEIGHT	STYLE
CHH641NBK	CHH641NGY	100mm	80mm	20mm	-
CHH642BBK	CHH642BGY	100mm	80mm	30mm	battery compartment
CHH643NBK	CHH643NGY	120mm	80mm	20mm	-
CHH644BBK	CHH644BGY	120mm	80mm	30mm	battery compartment





64-IP Gasket

- EPDM rubber gasket
- IP65 protection
- Operating temperature -20°C to +85°C

TYPE NO.	DESCRIPTION
CHH64GASK	64-IP Gasket

UNIVERSAL ENCLOSURES

HELD CASES

HEAVY DUTY ENCLOSURES

> DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

ENCLOSURES

SUBRACKS

CUSTOM SIZED ECNCLOSURES

CUSTOM SERVICES

Plastic End Caps