

- External enclosure for 2.5" HDDs and SSDs
- USB 3.0 Host interface up to 5 Gbit/s with UASP support
- New chipset supports SATA III
- Toolless HDD installation
- LED for power and HDD access
- HDD up to 9.5 mm height, capacity no limit
- Supports Windows & Mac
- Plug & Play and Hot Swap
- Including silicone protection sleeve

All in white

The IB-233U3-Wh presents itself as an elegant white 2.5" enclosure surrounded by a matching silicone sleeve. But the inner values dont fall short of anything. USB 3.0 with UASP support to make data transfer very fast and connecting the enclosure is easy play.

Technical data

 Model
 IB-233U3-Wh

 Article No.
 21244

 EAN code
 4250078163404

 Brand
 ICY BOX

Article text External enclosure for 2.5" SATA HDD/SSD with USB 3.0 interface and silicone protection sleeve

Colour White

HDD interface 1x 2.5" SATA I/II/III

HDD height Up to 9.5 mm
HDD capacity No limit
Hot Swap Yes
Plug & Play Yes

External data interface 1x USB 3.0 with UASP support Transfer rate USB 3.0 up to 5 Gbit/s
LED Power, HDD access

Operating system Windows und Mac Power connector Power via USB

Packing content: 1x IB-233U3-Wh, 1x USB cable, 1x manual, 1x silicone protection sleeve

Logistical data

Packing unit:20 pcs./cartonDimension/carton:395x277x230 mmTotal weight:4.7 kg/cartonDimension of packing box:190x130x40 mmGross weight (incl. packing):0.210 kgDimension of article:133x84x16 mm

Net weight: 0.106 kg Country of origin: China

RaidSonic Technology GmbH • Kurt-Fischer-Straße 50 • 22926 Ahrensburg / Germany Telefon: +49-(0)4102 -468 900 (Vertrieb) • Fax: +49-(0)4102 -468 901 • www.raidsonic.de Offers and deliveries are only done under our General Terms and Conditions. Errors and omissions excepted.



Import tax: 84733080

UASP