## **PRODUCT SPECIFICATION**

Brand Kasp

Product Range Hasp and Staples

Catalogue number 210

**Date** 15/03/2007



## **Range Description**

Traditional Hasp & Staples

## **Features**

- Hardened staple Extra protection from attack
- Chrome plated finish extra resistance to corrosion
- Concealed fixings added security
- Fixing screws included

These Hasp and staples are supplied display packed in sealed blisters or boxed



Item	Item Description	EAN No	Commodity	Carton
Number	·		code	Qty
K21075	Traditional hasp & staple 75mm – boxed	5013969902587	83024100	6
K21075D	Traditional hasp & staple 75mm – display packed	5013969901184	83024100	6
K21095	Traditional hasp & staple 95mm – boxed	5013969902594	83024100	6
K21095D	Traditional hasp & staple 95mm – display packed	5013969901191	83024100	6
K210115D	Traditional hasp & staple 115mm – display packed	5013969901177	83024100	6

Technical product					
information	Materials – steel with chrome plating – staple is case hardened				
	Security rating:				
	Security rating.				
	Security				
	Item rating rating				
	K21075 2				
	K21075D 2				
	K21095 4 K21095D 4				
	K210115D   5				
	Staple Hole Dia:				
	Staple Hole				
	I Item Dia				
	K21075 9				
	K21075D 9				
	K21095 13.4				
	K21095D 13.4				
	K210115D 13.4				
	Use environment- Light outdoor use				
	Use environment- Light outdoor use				
	Recommended applications- Cases, cupboards, lockers, toolboxes,				
	sheds etc.				
Standards compliance	None applicable				
User health and safety information	None applicable				
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations				
Material safety data	None applicable				
Warranty	KASP Hasp & staples are guaranteed against defects in manufacture and/or materials for 10 years				
	Damage caused through inappropriate use or attempted break in is not covered				
Country of origin	China				
, - 9					

## **Dimensional details**

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K21075	28	75	25	66	55	122	35	77
K21075D	28	75	25	66	110	30	170	86
K21095	40	95	33	133	55	122	35	145
K21095D	40	95	33	133	110	32	170	155
K210115D	47	32	117	183	110	40	210	213