

Product MD 325 G3

3 mm LED indicator color green

3 mm LED indicator
green
MD 325 G3
12-16
24-28
555
4.4
1 2
-25 +80
-30 +85


chip construction	GaP
forward current max. [mA]	25
reverse voltage max. [V]	4
luminous intensity typ. [mcd]	7 at 15 mA

Low cost LED indicator with ribbed nylon body for easy front panel mounting;

150 mm PVC leads *, AWG 26, black lead, cathode lead = blue

note

- all dimension are in millimeter
- \bullet tolerance is \pm 0.25 mm unless otherwise noted
- specifications are subject to change whithout notice
- version 1.0



© OSHINO LAMPS GmbH, Tennenloher Straße 19, D 90425 Nürnberg