

Product MD 577 G3

5 mm LED indicator color green

product-catalog	5 mm LED indicator
color	red
part no	MD 577 G3
forward current [mA]	12-16
forward voltage typ. [V]	24-28
wavelenght [nm]	565
rec. mounting hole Ø [mm]	6.35
panel thickness [mm]	1 3
operating temperature [°C]	-25 +80
storage temperature [°C]	-30 +85


chip construction	GaP
forward current max. [mA]	25
reverse voltage max. [V]	4
luminous intensity typ. [mcd]	25

Low cost LED indicator with ribbed nylon body for easy front panel mounting

150 mm PVC leads *, AWG 26, black lead, cathode lead = blue * for special lead length add appendix -Lxxx (xxx length in mm) to standard P/N

note

- all dimension are in millimeter
- tolerance is \pm 0.25 mm unless otherwise noted
- specifications are subject to change whithout noticeversion 1.0



© OSHINO LAMPS GmbH, Tennenloher Straße 19, D 90425 Nürnberg