


TABLE 1. DIMENSIONS

PART No.	A	B
MFC-16HF	24.89	17.78
MFC-20HF	30.0	22.86
MFC-26HF	37.6	30.48
MFC-30HF	42.7	35.56
MFC-34HF	47.8	40.64
MFC-40HF	55.4	48.26
MFC-50HF	68.1	60.96
MFC-60HF	80.8	73.66



NOTE1. APPLICABLE CONTACT AND WIRE
 SEE TABLE#2.

2. APPLICABLE CASE : MFC- () LH
 VERTICAL CASE : MFC- () LHP
 HORIZONTAL CASE : MFC- () LHP
 SKEW CASE : MFC- () WH
3. THIS DRAWING INDICATES MFC-16HF.
4. SPECIFICATION
 VOLTAGE RATING : AC 300V (r. m. s.)
 CURRENT RATING : 3A
 VOLTAGE PROOF : AC 1000V (r. m. s.)
 INSULATION RESISTANCE: 1000MΩ MIN. AT DC 500V
 CONTACT RESISTANCE : 10mΩ MAX.
 TEMPERATURE RATING : -40~+85℃
 HUMIDITY : 90% MAX.

TABLE 2. APPLICABLE CABLE AND WIRE

APPLICABLE WIRE	INSULATION DIA.	FINISH	
		FEMALE CONTACT	LOOSE PIECE TERMINAL
AWG#24~28	1.0~1.5mm	HKP-F103	HKP-F113
AWG#28~32	0.5~0.8mm	HKP-F403	HKP-F413
		HKP-F203A	HKP-F213A
		HKP-F303A	HKP-F313A

LTR. DATE	BY	REV. DESCRIPT	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE
			1	INSULATOR	PBT (GF)	1	UL94V-0 BLACK	

DATE	SCALE	UNIT	3RD. A. P
AUG.28.2000	4/1	mm (INCH)	

DR.	DE.	CHK.	CHK.	APP.

NAME		PART NO.	
HONDA TSUSHIN KOGYO CO., LTD.		MFC- (n) HF	