

**MNX ABS 125/60 HG**



Sample photo

**Order symbol:** ABS 125/60 HG  
**Product nbr:** 6081307  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074022868  
**EI. number:**  
 Finland: 3420531  
 Denmark: 8212023194  
 Italy: 7361055  
 Sweden: 2535730  
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
<b>mm:</b> 130	130	60		Ingress Protection (EN 60529): IP 66/67
<b>inch:</b> 5.1	5.1	2.4		Impact Resistance (EN 62262): IK 07
Materials:				Electrical insulation: Totally insulated
<b>Material:</b> ABS				Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b> RAL 7035				Flammability Rating (UL 746 C 5): UL 94 HB
<b>Cover colour:</b> RAL 7035				Glow Wire Test (IEC 695-2-1) °C: 650
<b>Cover screws material:</b> Polyamide				NEMA Class: NEMA 1, 4, 4X, 6
<b>Cover screws colour:</b> Grey				Certificates:
<b>Gasket material:</b> TPE				Fimko
Temperatures:				Europe EN 62208: 2003
<b>Short term:</b> -40 ... 80 °C				Gost R
<b>Continuous:</b> -40 ... 60 °C				
<b>Short term:</b> -40 ... 175 °F				
<b>Continuous:</b> -40 ... 140 °F				
Accessories:				
MIV 125	Mounting plate (Galvanized steel)			
MIN 10	DIN-15 Mounting rail			
MIV 10	DIN-35 Mounting rail			
FP A 125/130	Front plate (Aluminium)			
HFP 130	Front plate hinge series			
FP 22046	Wall fastening lug (4 pcs)			

