

MNX ABS 200/150 HG



Sample photo

Order symbol: ABS 200/150 HG
Product nbr: 6081329
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074014146
EI. number:
 Finland: 3420575
 Denmark: 8212023343
 Italy: 7361130
 Sweden: 6081329
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	255	180	150	Ingress Protection (EN 60529): IP 66/67
inch:	10.0	7.1	5.9	Impact Resistance (EN 62262): IK 07

Materials:

Material:	ABS
Base colour:	RAL 7035
Cover colour:	RAL 7035
Cover screws material:	Polyamide
Cover screws colour:	Grey
Gasket material:	TPE

Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): Yes
 Flammability Rating (UL 746 C 5): UL 94 HB
 Glow Wire Test (IEC 695-2-1) °C: 650
 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:

Short term:	-40 ... 80 °C
Continuous:	-40 ... 60 °C
Short term:	-40 ... 175 °F
Continuous:	-40 ... 140 °F

Certificates:
 Fimko
 Europe EN 62208: 2003
 Gost R

Accessories:

MIV 200	Mounting plate (Galvanized steel)
MIN 15	DIN-15 Mounting rail
MIN 20	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
MIV 20	DIN-35 Mounting rail
FP A 200/180	Front plate (Aluminium)
HFP 180	Front plate hinge series
FP 22046	Wall fastening lug (4 pcs)

