

MNX PC 125/35 LT



Sample photo

Order symbol: PC 125/35 LT
Product nbr: 6012907
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074022318
El. number:
 Finland: 3420431
 Denmark: 8212022360
 Italy: 7352040
 Sweden: 2535621
 Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		130	130	35	Ingress Protection (EN 60529): IP 66/67
inch:		5.1	5.1	1.4	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Black			NEMA Class: NEMA 1, 4, 4X, 6
Gasket material:		TPE			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C			Germanischer Lloyd (GL)
Continuous:		-40 ... 80 °C			Underwriters Laboratories
Short term:		-40 ... 250 °F			Det Norske Veritas
Continuous:		-40 ... 175 °F			Fimko
Accessories:					Europe EN 62208: 2003
MIV 125		Mounting plate (Galvanized steel)			UL Canada
MIN 10		DIN-15 Mounting rail			Gost R
MIV 10		DIN-35 Mounting rail			
FP A 125/130		Front plate (Aluminium)			
HFP 130		Front plate hinge series			
FP 22046		Wall fastening lug (4 pcs)			

